



Desiccant cartridge for moisture indication on small length elliptical waveguides E100 to E220 with air inlet G1/8

FEATURES / BENEFITS

- Desiccant cartridge
- Brass housing for desiccant cartridge
- Elbow adaptor G1"
- Sealing tape



Desiccant cartridge kit

Technical features**GENERAL SPECIFICATIONS**

| Product | | Distribution |
|-------------|--|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | | Desiccant cartridge to indicate high humidity. Granulate changes colour in the visual display from blue to violett in case the humidity in the closed waveguides system exceed 40%. In this case, purges of the waveguide with dry air (nitrogen gas) is recommended. The kit is unsuitable for drying closed waveguide systems with too high humidity. |

MECHANICAL SPECIFICATIONS

| | | |
|-----------------------|---------|--------------------------------|
| Dimensions, H x W x D | mm (in) | 65 x 33 x 33 (2.6 x 1.3 x 1.3) |
| Net Weight | kg (lb) | 0.23 (0.5) |

ACCESSORIES

| | | |
|----------------------|--|----------------------------|
| Accessory/Spare Part | | Desiccant cartridge DC-001 |
|----------------------|--|----------------------------|

[External Document Links](#)[Distribution](#)[Installation Instruction](#)[Notes](#)